

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2125153102](#)
Status: **Active**
Overview: [Mini-Fit Family Power Connectors](#)
Description: Mini-Fit Max Female Crimp Terminal, Tin over Nickel Plating, 16 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification 2125150001-PK-000 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [212515](#)
 Application Power, Wire-to-Board, Wire-to-Wire
 Crimp Quality Equipment Yes
 Overview [Mini-Fit Family Power Connectors](#)
 Product Name Mini-Fit Max
 UPC 193264598410

Physical

Durability (mating cycles max) 30
 Gender Female
 Material - Metal High Conductivity Copper
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.310/g
 Packaging Type Reel
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 2.42mm Max.
 Wire Size AWG 16
 Wire Size mm² N/A


Electrical

Voltage - Maximum 600V

Material Info

Reference - Drawing Numbers

Packaging Specification [2125150001-PK-000](#)
 Sales Drawing [2125150001-SD-000](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[212515 Series](#)

Use With

Mini-Fit Max Crimp Housing [212514](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for Mini-Fit MAX Receptacle Crimp Terminals, 16 AWG, UL1007 Wire	2133092300
Extraction and Activation Tool	638132700

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION