

Connection cable for SEW frequency inverters

Connection cable for SEW frequency inverters



Art. no.	BW2799
Specifications	
Pole number	4
Connection	1:1
Cable length	5 m
Electrical data connector	
Rated current	4A at 40°C
Rated voltage	160V
Pole number	4
Insulation resistance	≥ 100MΩ
General specific values connector	
Protection class	IP67, when mated and locked
Contact material	CuZn
Contact surface material	Ni, Au gal.
Material handle	TPU, UL 94, gray
Specific values cable	
Cable type	TPU, UL 20549, black
Conductor cross-section	4 x 0,34 mm ²
Core colors	brown, white, blue, black

Pin assignment:

MOVIMOT

