



**Part no.: 50031324**  
**KD 095-4**  
**Connector**



Figure can vary

## Contents

- Technical data
- Electrical connection

Part no.: 50031324 – KD 095-4 – Connector

## Technical data

### Electrical data

#### Performance data

Operating voltage	Max. 250 V AC/DC
Rated operating current	4,000 mA

### Connection

#### Connection 1

Type of connection	Connector with screw terminals
Thread size	M12
Type	Female
Material	Metal
Handle body material	Plastic
No. of pins	4 -pin
Encoding	A-coded
Design	Angled

#### Cable properties

Permissible conductor cross section	0.14 ... 0.75 mm <sup>2</sup>
-------------------------------------	-------------------------------

### Mechanical data

Design	L shape
Width across flats	15 mm
Dimension	27.5 mm

### Environmental data

Ambient temperature, operation	-25 ... 85 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 67
----------------------	-------

### Classification

Customs tariff number	85369010
eCl@ss 8.0	27069190
eCl@ss 9.0	27069190
ETIM 5.0	EC001578
ETIM 6.0	EC001578

## Electrical connection

Connection 1	
Type of connection	Connector with screw terminals
Thread size	M12
Type	Female
Material	Metal
Handle body material	Plastic
No. of pins	4 -pin
Encoding	A-coded

Part no.: 50031324 – KD 095-4 – Connector

<b>Connection 1</b>	
Design	Angled