



FIRST

DOUBLE
BEAM

CRISTALIA

oblong glass bowl

First

63606
(straight)

646 H 06
(articulated)
Black

63645
Metal grey

Cristalia

65645
Metal grey
Chromium-
plated
Frosted glass

**Double
beam**

637 H 06
Black

First : Budget version within
the halogen uplighters range

Cristalia : Diffuses a soft light thanks
to its frosted glass bowl filtering it
Great stability thanks to its ballasted
base of 6 kg and a diameter of 31 cm
Elegant feature with its elongated
bowl and its tapering shaft

Double beam : halogen uplighters
with double beam enabling direct
and indirect lighting

All of these uplighters are fitted with a
dimmer to adjust lighting

TECHNICAL FEATURES


- Halogen 300 W R75 max
- Average lifetime of the bulb 2000 hours
- Dimer on the wire
- Construction 2 wires + earth mounted
- Wire length : 2,10 m
- Material (**First and Double beam**) : Steel, black epoxy paint finish, (or metal grey for First) Aluminium reflector
- Material **Cristalia** : metallic post, frosted glass bowl, hubcaps made of steel
- Dimensions :
First : H 180 cm, Ø base 25 cm, Ø bowl 28 cm
Articulated First : H 160 to 186 cm, Ø base 33,5 cm, Ø bowl 28 cm
Cristalia : H 184 cm, Ø base 31 cm, bowl 42 x 21 cm (weight : 6 kg)
Double beam : Ø base : 30 cm. Ø post : 2.5cm.
Height of the post: 121 cm / Arm's length: 50.5 cm.
Ø bowl : 25 cm



Halogen tube R75 300 W max, high efficiency

LIGHTING

- Luminous efficacy : 22 lm/W
- Color temperature : 2900 Kelvin
- Color Rendering Index (CRI) : > 80



DIRECTIVES ORIGIN WARRANTY



1 YEAR

Unilux Malaysia

Halogen uplighters