

# DATA SHEET

## RUNPOCAM RC2

Multifunction camera - in lengths 10 m | 30 m | 50 m

Item no.: 10139 | 10140 | 10141



Click here Video



Click here Productinformation

W-BOX | Sortimo KOMPATIBEL

CAMERA WITH REEL + MONITOR + CASE + INCLUDED ACCESSORIES:



A. RUNPOGLIDER with front thread B. Micro memory card 8 GB / adapter C. Connection thread set (blind cap, inside and outside connection thread) D. SYSTEMGLIDER RC2 E. Fishing hook F. Magnet fishing-set G. High-performance 320-lumen rechargeable LED lamp (protection rating IP 67) H. Dual USB charging adapter 12 V I. Flexible attachment 12 cm J. USB / Micro-USB charging cable 3 m K. USB charging cable for LED battery Lamp L. Thread attachment RC 2 M. Dual USB charging adapter 230 V

### DATA

ITEM NO.	10139	10140	10141
CABLE LENGTH m	10 m	30 m	50 m
TOTAL WEIGHT KG	2,90 kg	3,54 kg	4,18 kg
CASE SIZE MM	B 395 mm   L 434 mm   H 135 mm		
MONITOR	3.5" TFT LCD Monitor 16 M color		
CAMERA PROBE	307.200 Pixel (640 x 480)		
ILLUMINATION	6 x LED (integrated in camera probe)		
PROTECTION CLASS	IP 67 (camera probe and cable)		
FIELD OF VIEW	64 °		
FOCUSSING DISTANCE	30 mm – 80 mm		
POWER SUPPLY	230 V or battery-operated (battery included)		
LANGUAGES	DE, EN, FR, ES, PT, IT, NL, DA, SE, NO, FI, PL, CS, HU, RU, IS, LT, SK, SLO, HR, TR		
EAN-CODE	9120045475555	9120045475562	9120045475579

### ADVANTAGES

- ✓ Protection class IP67
- ✓ Pipe inspection from Ø 14 mm (inside)
- ✓ Ventilation pipes, drainage pipes, sewage pipes and much more
- ✓ Also for cavity inspection and suspended ceilings
- ✓ Lengths 10 m, 30 m or 50 m
- ✓ Memory function/documented evidence
- ✓ Photo (JPG), Video (AVI), Audio
- ✓ Spool with camera cable can be easily unwound or rewound via the X BOARD series

### DESCRIPTION

RUNPOCAM RC2 multifunction camera with cable lengths of 10 m, 30 m and 50 m with coil incl. monitor bracket. In W-Boxx system case - compatible with Sortimo. Extra large 3.5" TFT LCD 16 m colour display, protection class IP67 (camera head and cable), battery operation up to 6 hours. Evidence preservation/storage function: photo, video and audio. CAMERA HEAD with 6 integrated LEDs, enclosed in robust stainless steel head (Ø 13 mm) with RTG Ø 6 mm internal thread. Compatible to all RUNPOTEC products with RTG Ø 6 mm thread (POWER REX, RUNPOSTICKS, RUNPO 1, glass fibre rod Ø 4.5 - 6 - 7.5 - 9 - 11 - 15 mm).

**Optimal field of application:** For pipe inspections over long distances of up to 50 m. As of 14 mm inner diameter (corresponds to empty pipe Ø 20 mm), but also for larger pipe cross-sections (ventilation systems, drainage systems, sewage pipes etc.). In combination with the RUNPOSTICKS, excellent for cavity wall inspections, suspended ceilings (above high ceiling profiles), manhole and underfloor ducts, maintenance and system inspections.

**Application video:** a short, very informative application video can be viewed by scanning the QR code or on www.runpotec.com.

**Scope of delivery:** RUNPOCAM RC2 with cable incl. reel in system case and incl. accessories: RUNPOGLIDER with front thread, system slide, LED-battery high performance 320 lumen lamp, Micro Memory Card 8 GB, magnetic catch set, connecting thread set RTG Ø 6 mm, catch hook, 2-fold USB charging plug 12 V, flexible attachment 12 cm, USB cable 3 m, 2-fold USB charging plug 230 V, threaded attachment RC 2, USB charging cable for LED-battery lamp

### INFORMATION

Combinable plug systems:

**RUNPO 1** Length 5 - 30 m

**POWER REX** Length 20 m | 30m | 40 m | 50 m

**Fibreglass rod Ø 4,5/6/7,5/9/11 mm** Length 30 up to 300 Meter

**RUNPOSTICKS** Paket: Comfort | Standard