




GRAVITY TOGGLE WITH RUBBER WASHER, 3.93", M8 ROD

CATALOG NUMBER

MTVB8100



CERTIFICATIONS



FEATURES

Complete with rod, nut, washer and load distribution block

Threaded rod is secured against unintentional removal

Approved for use in stationary fire protection systems (for pipes up to 2")

PRODUCT ATTRIBUTES

Article Number: 584455

Material: Steel

Finish: Electrogalvanized

Rod Size: M8

Length: 100 mm

Drill Bit Diameter: 22 mm

Static Load: 800 N


Ultimate Static Load: 20 kN

ADDITIONAL PRODUCT DETAILS

Static Load represents the maximum recommended load when fixed to a trapezoidal sheet.

The Ultimate Static Load value does not take into account the load-bearing characteristics of the supporting material. The appropriate safety factor is to be added to this load rating.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

Noord-Amerika

+1.800.753.9221

Optie 1 - de Zorg van de Klant

Optie 2 - Technische Steun

Europa

Nederland:

+31 800-0200135

Frankrijk:

+33 800 901 793

Europa

Duitsland:

800 1890272

Andere Landen:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Onze krachtige portefeuille van merken:

nVent.com **CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**

© nVent 2022. Alle nVent tekens en emblemen worden bezeten of door de nVent Diensten GmbH of zijn filialen vergunning gegeven. Alle andere handelsmerken zijn het bezit van hun respectieve eigenaars.

nVent reserves het recht specificaties zonder bericht te veranderen.