

UVC Germicidal T5

G8W T5
0000501



Product features

- Germicidal T5



PRODUCT OVERVIEW

Product name	G8W T5
Technology	Fluorescent
Lamp shape	Linear
Type	T5
Cap/Base	G5
Fixture rating	Enclosed
General application	Hospitality, Residential & Consumer, Retail
ETIM Class	EC002962
E-number FI	4943153
E-number SE	8359300
E-number Norway	3834245
Light colour	UV
Wattage (W)	8
Average life (Nominal) (h)	8000
Product EAN number	5410288005010

DATA TABLE

General data

Product name	G8W T5
Technology	Fluorescent
Lamp shape	Linear
Type	T5
Cap/Base	G5
Fixture rating	Enclosed
General application	Hospitality, Residential & Consumer, Retail
ETIM Class	EC002962
E-number FI	4943153
E-number SE	8359300
E-number Norway	3834245

Optical data

Light colour	UV
--------------	----

UVC Germicidal T5

G8W T5
0000501

Adjustable chromaticity N

Electrical data

Wattage (W)	8
Current (A)	0.145
Transformer required	Yes

Lifetime data

Average life (Nominal) (h)	8000
----------------------------	------

Physical data

Max. Length base to base (mm) - A	288.3
Length base to pin Min-Max (mm) - B	293.0-295.4
Max. Lamp Diameter (mm) - D	16
Weight (kg)	0.021

Packaging

Single packaging type	Carton
Product EAN number	5410288005010
Packaging single length / height (cm)	30.13
Packaging single width (cm)	1.9
Packaging single depth (cm)	1.93
Units per inner package	24
Packaging inner length / height (cm)	8.23
Packaging inner width (cm)	31.07
Packaging inner depth (cm)	12.67
DUN14 (outer)	15410288005017
Units per outer package	480
Packaging outer length / height (cm)	36.9
Packaging outer width (cm)	66.7
Packaging outer depth (cm)	33.8

Safety data

Recommendation for disposal at end of life	Applicable
Special purpose lamp	Yes
Suitable for household illumination	No

TECHNICAL DRAWINGS

