

Nuts

For ‚Rhombus‘ T-grooves



Application:

For inserting sliding block from above through the neck of the T-groove.

Version:

- Tempered
- The reduced contact surface in the T-groove results in a lower load capacity compared with comparable DIN 508 sizes.



Art. no.	26194 075
Nominal dimension of groove	28 mm
Slot nut width	27.7 mm
Thread dimension	M20
Height	36 mm
Slot nut height	18 mm
Length	44 mm
Property class	8

EAN-Code

4020772084738