

LED work lamp "Spotlight"

With and without dimmer



Execution:

- High-performance LED 2 W, 250 lumens, colour temperature: daylight white, approx. 5500 Kelvin
- Glare- and flicker-free, low-reflection, with 24-V power supply unit
- Rubber-coated 66-mm magnetic base with adhesive force of 180 N
- Total length 600 mm, lamp head 28 mm
- Chip life min. 50,000 hours.
- Ref. no. 170: No dimmer
- Ref. no. 172 : With dimmer (continuously variable)

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



Art. no.	56879 172
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/44D
Power rating	2 W
Arm length	501 mm
IP protection class	IP 65
Dimmable	Yes
Gross Weight	0.650 kg
Product Group	51D

EAN

4260131238086