

Belt sanding machine GIS 75



Application:

Belt sanding machine for daily use. First-class product and work quality distinguish the robust GIS 75 belt sander. No option for modular expansion, making it very economical to buy.

Version:


- patented belt tensioning system
- robust 4 kW motor, 400 V, 50 Hz
- low-vibration
- with emergency stop switch

Advantage:

- especially suited for high-performance belt sanding
- high degree of operational safety provided by numerous safety devices (CE certificate)
- Commissioned without electrically qualified personnel
- user-friendly

Delivery:

incl. machine foot, CEE plug (16 A), 1 sanding belt (2000 mm, grain 36)



Art. no.	78238 010
Model	GRIT GIS 75
Max. sanding belt width	75 mm
Grinding belt length	2000 mm
Max. belt speed	30 m/s
Weight	65 kg

EAN-Code

4014586878126