



▪ Part Number	GE85-C
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Military Specification Nylon Grommet Edging in 12.75" strips.
▪ Product Type	Grommet Edging
▪ Material	Nylon 6.6
▪ Color	Natural
▪ Military Specification	MS21266-2N
▪ Height (In.)	0.16
▪ Height (mm)	3.9
▪ Length (In.)	12.75
▪ Length (mm)	323.9
▪ Width (In.)	0.18
▪ Width (mm)	4.5
▪ CE Compliant	No
▪ Flammability Rating	V-2
▪ Outside Depth (In.)	0.155
▪ Outside Depth (mm)	3.9
▪ Outside Width (In.)	0.175
▪ Outside Width (mm)	4.5
▪ Panel Thickness Range (In.)	0.052 – 0.085
▪ Panel Thickness Range (mm)	1.3 – 2.2
▪ Pricing Description	Grommet Edging, Slot Strip, Nylon, Natural
▪ Temperature Range	-40°F – 149°F (-40°C – 65°C)
▪ Type	Grommet Edging
▪ Min. Order UOM	PC
▪ Min. Order Qty.	100
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>