



MATERIAL

Insulator : PBT+30% Glass fiber
 Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
 Insulation Resistance : 5000MΩMin. at DC 500V
 Contact Resistance : 20mΩMax. at DC 100mA
 Dielectric Voltage : 500V AC for one minute
 Operation Temperature : -55°C to +105°C

RoHS Compliant		HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准 HELEN		TOLERANCE 容許公差 0 ±0.30 .00 ±0.20 ANG. ±3°	PART NAME 品名 2.54mm MINI JUMPER 2P H.6.0mm OPEN COVER ROHS
DWG. 製圖 ABBY	SCALE 比例 參考	UNIT 單位 MM	PART NO. 料號 C2700-02AAXX00R
DATE 制表日 2016/04/07	PAGE 張數 1 OF 1	REV. 版本 A	