


Blade terminal

Blade Terminals, Insulated



FEATURES:

Double crimp with copper sleeve on barrel

SPECIFICATION:

Material	Brass
Surface material	Tin-plated

PRODUCT RANGE:

Art. Nr.	Contact	Cross-section	Colour	Insulation material	Temperature range	Voltage	Thickness
RND 465-00007	2.8 x 0.5 mm	0.5...1.5 mm ²	red	Vinyl	max. +105 °C	600 V	0.5 mm
RND 465-00008	4.8 x 0.5 mm	0.5...1.5 mm ²	red	Vinyl	max. +105 °C	600 V	0.5 mm
RND 465-00080	4.8 x 0.8 mm	0.5...1.5 mm ²	red	Vinyl	max. +105 °C	600 V	0.4 mm
RND 465-00082	6.3 x 0.8 mm	0.5...1.5 mm ²	red	Vinyl	max. +105 °C	600 V	0.4 mm
RND 465-00083	4.8 x 0.8 mm	1.5...2.5 mm ²	blue	Vinyl	max. +105 °C	600 V	0.4 mm
RND 465-00084	6.3 x 0.8 mm	1.5...2.5 mm ²	blue	Vinyl	max. +105 °C	600 V	0.4 mm
RND 465-00085	6.3 x 0.8 mm	4...6 mm ²	yellow	Vinyl	max. +105 °C	600 V	0.4 mm
RND 465-00088	2.8 x 0.8 mm	0.5...1.5 mm ²	red	Vinyl	max. +105 °C	600 V	0.4 mm