

▶ (RTS) Surface Type

RT-K02 Si+Si.SKP5



Max. operating temperature : -50 °C / +200 °C
Standard cable types : Si + Si
Standard cable length (K) : 2m
Sensor type : DIN/EN60751 Class "B" 1xPT-100

▶ (RTS) Surface Type

RT-K02.SKP5



Max. operating temperature : -50 °C / +400 °C
Standard cable types : Fiber glass + braided wire
Standard cable length (K) : 2m
Sensor type : DIN/EN60751 Class "B" 1xPT-100