

M12 male 0° shielded B-cod. with cable, Profibus

PUR 1x2xAWG23 shielded vt torsion UL/CSA 5m


M12

Male straight


PROFIBUS, B-coded

2-pole, shielded

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request. Further cable lengths on request.

[Link to Product](#)**Illustration**

Male



Product may differ from Image

Approvals



More Info



Form

14051

Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M12 × 1 mm (recommended torque 0.6 Nm) self-securing
Protection	IP67 inserted and tightened (EN 60529)

Cables

Cable number	843
No./diameter of wires	1 × 2 × Ø 0.64 mm, (violet)

Wire isolation	PE (rd, gn)
Torsion	1 Mio. \pm 360°/m
Jacket Color	violet
Shore hardness outer jacket	87 \pm 3A
Material (jacket)	PUR (UL/CSA), Torsion
Outer diameter	approx. 8.0 mm
Bend radius (fixed)	8 \times outer \varnothing
Bend radius (moving)	12 \times outer \varnothing
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-20...+50 °C
Shielded	yes

General data

Temperature range	-25...+85 °C, depending on cable quality
-------------------	--

Commercial data

country of origin	DE
customs tariff number	85444290
minimum order quantity	1