

AC-1 CONTACTOR, 4-POLE, 1000 A, MAIN CONTACTS 4 NO, AUXILIARY CONTACTS 2NO+2NC, AC OPERATION AC 230...240V, 50HZ



Figure similar

General technical data:

Protection class IP on the front		IP00
Ambient temperature during operation	°C	-25 ... +55
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		K
Equipment marking acc. to DIN EN 61346-2		Q
Number of poles for main current circuit		4
Operating current at AC-1 at 400 V		
• at ambient temperature 40 °C Rated value	A	1 000

Main circuit:

Number of NC contacts for main contacts		0
Number of NO contacts for main contacts		4
Operating current at AC-3 at 400 V Rated value	A	700
Operating power		
• at AC-3 at 400 V Rated value	kW	370
• at AC-1 at 400 V Rated value	kW	655

Control circuit/ Control:

Control version of the switch operating mechanism		conventional
Type of voltage of the control supply voltage		AC
Control supply voltage frequency		
• 1 Rated value	Hz	50
• 2 Rated value	Hz	50
Control supply voltage		
• with AC		

— at 50 Hz		
— Rated value	V	230 ... 240
Number of NC contacts for auxiliary contacts		
• lagging switching		0
• instantaneous contact		2
Number of NO contacts for auxiliary contacts		
• leading contact		0
• instantaneous contact		2



Auxiliary circuit:

Number of NC contacts for auxiliary contacts		2
Type of electrical connection for main current circuit		screw-type terminals
Type of electrical connection for auxiliary and control current circuit		screw-type terminals
Identification number and letter for switching elements		22

Mechanical data:

Mounting type		screw fixing
Mounting type Side-by-side mounting		Yes
Width	mm	266
Height	mm	272
Depth	mm	225.5

Certificates/ approvals:

General Product Approval	Test Certificates	other		
 ccc		Special Test Certificate	Declaration of Conformity	Environmental Confirmations

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TK17420AU0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TK17420AU0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TK17420AU0&lang=en

last modified:

16.03.2015