

Tango 49

2G/3G/4G 96mm length panel mount antenna



Key Features

- Whip style panel mounting
- All 4G frequencies
- 2G and 3G frequency coverage
- 28mm base diameter

General Description

The Tango 49 is strong slim antenna ideally suited to mounting remotely from the device to maximise signal strength. The antenna can also be mounted directly into alarm/control panels.

The Tango 49 has a wide operating temp between -45°C and 85°C making it extremely versatile for global location.

The antenna can be supplied with alternative cable lengths or connector types for volume orders.

Additional Considerations

- Extremely versatile for global location
- Strong but slim antenna

Tango 49

2G/3G/4G 96mm length panel mount antenna


Electrical Specifications

Temperature Range:	-45°C - +75°C
Impedance:	50 Ohm
Gain:	2.16dBi
VSWR:	<2:1
Frequency Range:	698 - 960MHz 1710 - 2600 MHz
Polarization:	Vertical

Mechanical Specifications

Dimensions:	L96 x 28mm Ø
Connector:	SMA
Cable:	RG174
Mounting Method:	M12 15mm Stud
Max recommended material thickness	7mm

VSWR



Ordering Details

Part Number	Description
TANGO49/2.5M/SMAM/17	2G/3G/4G 96mm length panel mount antenna