

Product data sheet

Item No. 92.257.3003.1

Cable assembly GST18I5K1B- 15 30SW

geis® Connection cable female - free end; length: 3m; type GST18I5; 5-pole; 250/400 V / 16 A; colour of coding: black with black strain-relief; cable: H05VV-F 5G1,5, colour: black



Item No.	92.257.3003.1
EAN	4015573587854
Order Unit	15 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 1
Interlockable	Yes
Color of coding/ contact carrier	Black
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	5
Nominal cross section conductor	1.5 mm <sup>2</sup>
Degree of protection (IP)	IP40
Wire strip length	9 mm
sheath strip length	35 mm
Preparation of conductor ends	Ultrasonically compressed wire ends
Cable type	H05VV-F

Cable colour	Black
Cable diameter	10.1 mm
Version of cable	Female - free end
Type of cord set	Connection cable
Version cable end 1	GST18i5 socket
Version cable end 2	Free end

**Material**

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

**Dimensions**

Total length	3 m
--------------	-----

**Technical drawing**
