


ToLEDo Stick

TOLEDO STICK V3 1055LM 865 E27 SL
0029032



Product features

- A bright, all-around lighting solution for living rooms, wall lights, ceiling lights, compact and decorative luminaires • Quick and easy replacement of compact fluorescent, halogen or incandescent lamp • 15,000H average rated life • 85% energy savings compared to incandescent • Last 50% longer and consume 45% less energy compared to compact fluorescent integrated lamps • A+ energy rating • Omni-directional light distribution • Non-dimmable



PRODUCT OVERVIEW

Product name	TOLEDO STICK V3 1055LM 865 E27 SL
Technology	LED
Watt (Rated) (W)	11
Cap/Base	E27
Fixture rating	Open
General application	Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4740876
Warranty	3 years
Luminous flux (lm)	1150
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Wattage (W)	11
Product Voltage (V)	230
Average life (Nominal) (h)	15000
Product EAN number	5410288290324

DATA TABLE

General data

Product name	TOLEDO STICK V3 1055LM 865 E27 SL
Technology	LED
Watt (Rated) (W)	11
Cap/Base	E27
Fixture rating	Open
General application	Hospitality, Residential & Consumer
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4740876
Warranty	3 years

Optical data

Luminous flux (lm)	1150
--------------------	------

ToLEDo Stick

TOLEDO STICK V3 1055LM 865 E27 SL
0029032

Luminous flux (Rated) (lm)	1150
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Lumen maintenance at end of nominal life (%)	70

Electrical data

Wattage (W)	11
Equivalent watt (W)	80
Starting time (max) (s)	0.5
Warm-up time to 60% of full light (max) (s)	1
Product Voltage (V)	230
Lamp power factor	0.5
No. Of switching cycles before premature failures	>50000
Inrush Current (A)	4.15
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	2
Max. Luminaires per 16A C Breaker	3
Max. Luminaires per 20A C Breaker	4

Lifetime data

Average life (Nominal) (h)	15000
Average life (Rated) (h)	15000

Physical data

Nominal Product Length (mm)	137
Nominal Product Diameter (mm)	45
Weight (kg)	0.069

Packaging

Single packaging type	Mix blister(20% carton, 80% pl)
Product EAN number	5410288290324
Packaging single length / height (cm)	4.6
Packaging single width (cm)	4.6
Packaging single depth (cm)	14.4
DUN14 (outer)	15410288290321
Units per outer package	10
Packaging outer length / height (cm)	24.5
Packaging outer width (cm)	10.2
Packaging outer depth (cm)	15.8

Safety data

Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures



ToLEDo Stick

TOLEDO STICK V3 1055LM 865 E27 SL

0029032
