



Quality Products. Service Excellence.

Four Post Mounting Sliding Shelf *RSUS Series*

Up to 130 lbs (59 kg) Weight Capacity

Features



- Constructed of 16 gauge steel.
- Easily gain access to non rack mountable equipment in a server cabinet or 4-post rack rack.
- Requires two (2) pairs of mounting rails.
- Heavy duty ball bearing slides included
- The slides feature a stopping mechanism, preventing the shelf from accidentally falling out of the slide tray.
- Up to 130 lbs (59 kg) in weight capacity.
 - Slides are tested to BIFMA Standards with load capacity @ 12 times/minute for 55000 cycles minimum.
- Rugged textured powder paint finish.
- TAA compliant for GSA Schedule purchases.
- RoHS and REACH compliant.
- Manufactured in North America.



Are you looking for a 2-Post sliding rack shelf? Take a look at the **RSP Series**.

Gallery



Accessories

- Mounting Hardware
- Extender Bracket for Sliding Shelves
- Hook and Loop Roll
- Chassis Sliding Rack Rail Kit

Solid Part No.	Vented Part No.	Overall Dimensions		Shelf Dimensions			Rail Mounting Depth		Slide Travel	Weight Capacity
		Height	Width	Height	Width	Depth	Min	Max		
RSUS1918BK1	RSVS1918BK1	2.68	18.89	1.50	16.64	18.12	6.00	20.00	18.00	130 lbs (59 kg)
RSUS1921BK1	RSVS1921BK1	2.68	18.89	1.50	16.64	21.00	12.00	21.00	20.00	114 lbs (52 kg)
RSUS1926BK1	RSVS1926BK1	2.68	18.89	1.50	16.64	26.12	16.00	27.75	26.00	94 lbs (43 kg)
RSUS1931BK1	RSVS1931BK1	2.68	18.89	1.50	16.64	31.00	18.00	28.00	28.00	85 lbs (39 kg)

Data subject to change without notice