

## TORX-Screwdriver

L = with bore hole in the tip



No.	Size	Blade-length mm	for metric thread	Handle size mm	Weight g
6-979	T 5	55	M 1.6 - 2	100 x 21	25
6-981	T 6	65	M 2	100 x 21	29
6-982 L	T 7	65	M 2.5	100 x 21	29
6-983 L	T 8	75	M 2.5	100 x 21	29
6-984 L	T 9	75	M 3	100 x 21	29
6-985 L	T 10	85	M 3-3.5	100 x 21	32
6-986 L	T 15	85	M 3.5-4	100 x 21	34
6-987 L	T 20	100	M 4-5	100 x 21	35
6-988 L	T 25	100	M 4.5-5	107 x 27	57
6-989 L	T 27	105	M 4.5-5-6	107 x 27	63
6-991 L	T 30	105	M 6-7	114 x 32	90



6-979

## Wrenches long

No.	Size	Blade-length mm	Handle size mm	Weight g
6-101	3.0	125	100 x 21	47 g
6-102	4.0	125	100 x 21	49 g
6-104	5.0	125	100 x 21	50 g
6-105	5.5	125	100 x 21	50 g
6-106	6.0	125	100 x 21	61 g
6-107	7.0	125	100 x 21	78 g
6-108	8.0	125	107 x 27	102 g




6-101

4-530

### 7-piece screwdriver set from the series EUROline-Power visible packed in a carton box

Content: 1 Slotted screwdrivers 100 x 5.5 mm, 125 x 6.5 mm  
1 Slotted screwdrivers 100 x 4.0 mm, 150 x 5.0 mm  
1 Cross-recess screwdriver PH1 and PH2  
and 1 voltage tester, 60 x 3.0 mm

Weight: 520 g



4-530