

TY5244MXR



CABLE TIE 30LB 14.5IN UV BLACK NYL

General Information

Extended Product Type	TY5244MXR
Product ID	7TCG009110R0025
EAN	5414363065494
Catalog Description	CABLE TIE 30LB 14.5IN UV BLACK NYL
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 368.3mm (14.5 Inches), Width of 3.61mm (0.142 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Euroslot Packaging

Ordering

EAN	5414363065494
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.004 lb 1.814 g
--------------------	--------------------

Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	13 in 330 mm
Package Level 2 Height	13 in 330 mm
Package Level 2 Depth / Length	14 in 356 mm

Additional Information

Brand / Label	Ty-Rap
Color	Black
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	TY-RAP FASTENING

Product Type	Standard
Surface Finishing	Untreated
Tensile Strength	40 lb 180 N
Thickness	0.05 in 1.31 mm
UPC	786210468556

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY5244MXR
Instructions and Manuals	TY5244MXR

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

