

# Adapter USB

## ZNNG021

Part Number



### Technical Data

#### Electrical Data

Max. Current Consumption	90 mA
Temperature Range	0...45 °C
Reverse Polarity Protection	yes
Number of IO-link ports	1
Interface	USB/NFC
Protection Class	III

#### Mechanical Data

Material	Plastic
Degree of Protection	IP20
Scope of delivery	USB extension cord type A/A
Packaging unit	1 Piece

USB Interface

- **Wireless settings via NFC**

### Complementary Products

Software

