

J3500-SMD Rechargeable Slim Light

Redashe

The J3500-SMD – Has 15 high output SMD's with two power settings, the first of which is exceptionally bright giving approximately 600 lumens and will run for 4 hours. The 2nd setting will reduce the light output but increase the run time to 7 hours. The built in battery monitor located in the handle gives a clear visual indication of battery status. Recharging the light will take 5.5 hours; this can be done using the included USB plug and cable or any USB port. The unit is constructed from ABS plastic and aluminium making the unit very robust. The aluminium light wand is extremely slim (7mm) allowing the light access to difficult to reach areas. The built in hook and magnet allow for hands free working in confined areas. The light pivots in the centre through 150° each step is thirty degrees this allows the light to be directed exactly where it is required.



FEATURES:

- Ultra slim (7 mm) designed to access difficult areas
- Robust aluminium body
- 15 High output SMD's, approximately 600 lumens (max 7.5w)
- High capacity lithium-ion rechargeable battery for longer life and consistent power
- Powerful magnet on base for hands free operation
- Top mounted 360° rotating hanging hook for hands free operation
- Lamp body pivots up to 150° in 30° increments, allowing the operator to direct the strip light accurately
- Built in automatic charging cut off, protecting the battery from overcharging
- Built in battery level indicator on the handle
- Supplied complete with AC/DC adaptor, 100 - 240V, USB plug and USB charging lead



TECHNICAL DATA	
Power supply type	Rechargeable
Materials	Aluminium / ABS plastic
Battery	4400 mAh
Charging system	Input: 100-240VAC Output: 5V 2A
Charging time	5.5 hours
Operation time	Full brightness mode: 4 hours Reduced brightness mode: 7 hours
SMD - LED	15 - 7.5W