

BLINDNIETE



FLACHRUNDKOPF (~ DIN EN ISO 15977)

BLIND RIVETS

DOMED HEAD (~ DIN EN ISO 15977)

RIVETS AVEUGLES

TÊTE PLATE (~ DIN EN ISO 15977)



Aluminium AIMG 3,5
Aluminium AIMG 3,5
Aluminium AIMG 3,5

Stahl verzinkt
Steel zinc plated
Acier zingué

Ø 6,4 mm

D1 = 6,4 + 0,08 / - 0,15 mm

D2 = 13,0 + 0 / - 1,5 mm

k = 1,8 + / - 0,4 mm

d = 3,85 mm

P = ≥ 27,0 mm

L = + 1,0 / - 0,2 mm

6,5 mm

	F-Max		CODE				
6,4 x 10,0 mm	16,4 mm	2,0 - 5,0 mm	70701 64100	2600 N	4000 N	250	2500
6,4 x 12,0 mm	18,4 mm	4,0 - 6,0 mm	70701 64120			250	2500
6,4 x 15,0 mm	21,4 mm	6,0 - 9,0 mm	70701 64150			250	2500
6,4 x 16,0 mm	22,4 mm	7,0 - 9,5 mm	70701 64160			250	2500
6,4 x 18,0 mm	24,4 mm	9,0 - 12,0 mm	70701 64180			250	2500
6,4 x 20,0 mm	26,4 mm	11,0 - 14,0 mm	70701 64200			250	2500
6,4 x 22,0 mm	28,4 mm	13,0 - 16,0 mm	70701 64220			250	2500
6,4 x 26,0 mm	32,4 mm	16,0 - 20,0 mm	70701 64260			250	2500
6,4 x 30,0 mm	36,4 mm	18,0 - 24,0 mm	70701 64300			250	2500
6,4 x 35,0 mm	41,4 mm	24,0 - 30,0 mm	70701 64350			100	1000
6,4 x 40,0 mm	46,4 mm	30,0 - 35,0 mm	70701 64400			100	1000