

Sales Outline DrawingRevision **B****Specifications:**

Oscillation Frequency (Hz)	2900 ± 500
Operating Voltage (Vdc)	18 ~ 28
Rated Voltage (Vdc)	24
Current Consumption (mA/max)	30 at Rated Voltage
Sound Pressure Level (dB/min)	100 at 30cm at Rated voltage
Tone/Pulse Rate (Hz0)	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 777D plastic resin (Color: Black)
Lead Wires	28 AWG RED & BLACK
Weight (Grams)	13.2
Options	For other options contact factory

Dimensions: (units: mm)**ROHS Compliant**