


**Triaxial Male to Three Alligator Test Clips, Double Shielded**


Model#	Cable Type	Lugs	Length
4725	Triaxial	2	36in (0.9m)
5342	Triaxial	3	36in (0.9m)



**Rating:** Maximum voltage for *hands free use*: 150 Vrms\*.  
**Jaw Opening:** 0.30in (7.62mm) Max.  
**Triaxial:** *Body/Fittings:* tarnish resistant nickel-plated brass; *Intermediate and Center Contacts:* gold-plated brass; *Dielectric:* PTFE.  
 See chart on page 6 for additional wire and cable specifications.

**BNC Male with Molded Strain Relief to Micrograbber® Test Clips**

Model#	Length
4777-C-24	24in (0.6m)
4777-C-36	36in (0.9m)
4777-K-24	24in (0.6m)
4777-K-36	36in (0.9m)
4777-K-48	48in (1.2m)



**Rating:** Maximum voltage for *hands free use*: 150 Vrms\*.  
**BNC:** *Body:* tarnish resistant nickel-plated brass; *Center Contact:* gold-plated brass; *Dielectric:* PTFE.  
**Strain Relief:** PVC molded directly to cable and connectors.  
**Micrograbber:** *Contacts:* beryllium gold-plated copper; *Insulation:* glass filled nylon.  
**Colors:** One black and one red.  
 See chart on page 6 for additional wire and cable specifications.

**Triaxial Male Cables**


Model#	Cable Type	Lugs	Length
5223-36	Triaxial	3	36in (0.9m)
5223-60			60in (1.5m)
5054-36	Triaxial	2	36in (0.9m)
5054-60			60in (1.5m)



**Rating:** Maximum voltage for *hands free use*: 500 Vrms\*.  
**Triaxial:** *Body/Fittings:* tarnish resistant nickel-plated brass; *Intermediate and Center Contacts:* gold-plated brass; *Dielectric:* PTFE.  
**Cable Type:** Double Shielded, 50Ω, RG58A/U.  
**Colors:** 5223: Yellow, 5054: Yellow.  
 Triaxial to BNC Adapters on page 28.  
 See chart on page 6 for additional wire and cable specifications.

**BNC Male with Molded Strain Relief to Alligator Test Clips**


Model#	Length
4531-C-18	18in (0.5m)
4531-C-24	24in (0.6m)
4531-C-30	30in (0.76m)
4531-C-36	36in (0.9m)
4531-C-48	48in (1.2m)
4531-C-60	60in (1.5m)



**Rating:** Maximum voltage for *hands free use*: 150 Vrms\*.  
**Jaws Opening:** 0.3in (7.62mm) max.  
**BNC:** *Body:* tarnish resistant nickel-plated brass; *Center Contact:* gold-plated brass; *Dielectric:* PTFE.  
**Strain Relief:** PVC molded directly to cable and connectors.  
**Alligator:** *Body:* steel-plated nickel.  
**Colors:** Vinyl boots: one black and one red.  
 See chart on page 6 for additional wire and cable specifications.

**BNC Male with Molded Strain Relief to Minipincer® Test Clips**

Model#	Length
5423-C-24	24in (0.6m)
5423-C-36	36in (0.9m)
5423-C-48	48in (1.2m)



**Rating:** Maximum voltage for *hands free use*: 300 Vrms\*.  
**BNC:** *Body:* tarnish resistant nickel-plated brass; *Center Contact:* gold-plated brass; *Dielectric:* PTFE.  
**Strain Relief:** PVC molded directly to cable and connectors.  
**Minipincer:** *Contacts:* beryllium gold-plated copper; *Insulation:* glass filled nylon.  
**Colors:** One black and one red.  
 See chart on page 6 for additional wire and cable specifications.

