

Han E High Temp female contact 20 AWG



Part number	09 33 800 6220
Specification	Han E High Temp female contact 20 AWG
HARTING eCatalogue	https://b2b.harting.com/09338006220

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Contacts
Series	Han E [®] High Temp
Type of contact	Crimp contact

Version

Gender	Female
Contact identification	No groove
Manufacturing process	Turned contacts

Technical characteristics

Conductor cross-section	0.5 mm²
Conductor cross-section	AWG 20
Rated current	≤16 A
Contact resistance	≤1 mΩ
Stripping length	7.5 mm

Material properties

Material (contacts)	Copper alloy
Surface (contacts)	Silver plated
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Charifications	IEC 60664-1
Specifications	IEC 61984

Commercial data

Packaging size	100
Net weight	1.62 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140052642
ETIM	EC000796
eCl@ss	27440204 Contact for industrial connectors