

## Sylmaster T8 Christmas Tree Louvre (LS) - Electronic Ballast

T26 2x58W G13  
0055088



### Product features

- Sylmaster T8 Christmas Tree Louvre (LS) - Electronic Ballast



## PRODUCT OVERVIEW

Product name	T26 2x58W G13
Technology	Fluorescent
Cap/Base	G13
Housing	Steel
Mount	Ceiling surface mounting
Environment	Interior
General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
Warranty	2 years
Fixture luminous flux (lm)	6100
Luminaire efficacy (lm/W)	55
LOR (%)	61
Light colour	N/A
Light source included	Fixture without Lightsource
Total power consumption (W)	110
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Dimmable	No
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5410288550886

## DATA TABLE

### General data

Product name	T26 2x58W G13
Technology	Fluorescent
Cap/Base	G13
Housing	Steel
Mount	Ceiling surface mounting
Environment	Interior

## Sylmaster T8 Christmas Tree Louvre (LS) - Electronic Ballast T26 2x58W G13 0055088

General application	Education, Hospitality, Office, Retail
ETIM Class	EC002892
Warranty	2 years

### Optical data

Fixture luminous flux (lm)	6100
Luminaire efficacy (lm/W)	55
LOR (%)	61
Light colour	N/A
Adjustable chromaticity	N

### Electrical data

Light source included	Fixture without Lightsource
Total power consumption (W)	110
Mains voltage (V)	220-240V
Electrical protection	Class I
Control gear type	Electronic ballast
Control gear mounting	Integral
Transformer required	Yes
Dimmable	No
Glow Wire Test (°C)	960
Nominal Frequency (Hz)	50/60Hz

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Nominal Product Length (mm)	1550
Nominal Product Width (mm)	202
Nominal Product Height (mm)	85
Weight (kg)	5.08

### Packaging

Single packaging type	Carton
Product EAN number	5410288550886
Packaging single length / height (cm)	155.0
Packaging single width (cm)	9.0
Packaging single depth (cm)	21.0
DUN14 (outer)	05410288550886
Units per outer package	1
Packaging outer length / height (cm)	155.0
Packaging outer width (cm)	9.0
Packaging outer depth (cm)	21.0

## PHOTOMETRY

