

Drill vices

Mechanical clamping system

ORION[®]

Application:

For light machining work on drill presses and pillar drills.

Execution:

- Made from grey cast iron
- Precise clamping thanks to long flat rail guide
- Clamping jaws with steps and vee blocks
- Operate by hand or by toggle lever

Delivery:

1 pc. Drill vice



Art. no.	28665 060
Brand	ORION
Manufacturer Part Number	28665060
Jaws width	65 mm
Clamping width	70 mm
Jaws height	25 mm
Jaws thickness	12 mm
Body length	160 mm
Body height	47 mm
Body width	133 mm
Max. length	252 mm
Max. flute spacing	106 mm
Min. flute spacing	92 mm
Chip flute width	9 mm
Weight	2.5 kg
Gross Weight	2.600 kg
Product Group	282

EAN

4039247171187