

Drawer cabinets

Stationary



Application:

For day-to-day heavy-duty use in workshops

Version:

- All drawers with full extension
- Individual drawer lock as standard feature to prevent the cabinet from tipping over
- Perforated, slotted drawers provide a secure hold
- Very robust construction for a wide variety of applications and very demanding requirements

Advantage:

- Optimum wall height to keep items from falling out and getting lost
- Folding handle strips for simple, clean and protected labelling
- High quality - made in Germany and Swiss-made
- Runs perfectly smoothly and easily due to the lack of crossbars on the differential extension slide
- Full extension - clear overview and optimal access



Art. no.	50301 785
Number of drawers	11 PCS
Height	1450 mm
Width	1193 mm
Depth	725 mm
Height x width x depth	1450 x 1193 x 725 mm
Draw width (inner dimension) x drawer depth (inner dimension)	1080 x 600 mm
Load-carrying capacity per drawer	200 kg
Drawer lock	Standard
Drawer front height	1 x 150 mm, 1 x 125 mm, 1 x 75 mm, 5 x 100 mm, 2 x 150 mm, 1 x 200 mm
Cabinet colour	Light grey RAL 7035
Colour of front	Light grey RAL 7035
Opening/closing system	Key Lock
Clear height	1350 mm
LISTA unit	64 x 36 E

EAN-Code

7612269078961