

## Safety coupling eSafe series 320 – DN 7.6, steel, zinc-plated

In line with ISO 4414 and EN 983



### Application:

For connecting hoses to compressed air tools and compressed air machines.

### Execution:

- High-performance coupling relieving pressure before uncoupling to eliminate the risk of hose backstroke
- Male threads on the coupling and nipple are factory-fitted with thread seals

### Advantage:

- Pressure relief for improved safety
- Very high flow capacity
- Rugged and durable



<b>Art. no.</b>	<b>75135 021</b>
<b>Brand</b>	CEJN
<b>Manufacturer Part Number</b>	103202154
<b>Type</b>	with male thread
<b>Connection thread</b>	R 3/8 inch
<b>Flow capacity</b>	2250 l/min
<b>Max. operating pressure</b>	16 bar
<b>Thread length</b>	11 mm
<b>Length</b>	68 mm
<b>Width across flats</b>	20 mm
<b>Min./max. temperature resistance</b>	-20 to +100 °C
<b>Gross Weight</b>	0.126 kg
<b>Product Group</b>	7A1

### EAN

7391390044792