



# MASTER - LED HID SON-T



#### MAS LED SON-T IF 4Klm 23W 740 E27

Philips MASTER - LED HID SON-T lamps are an easy LED solution with a short payback period to replace High-Intensity Discharge (HID) and High-Pressure Sodium (SON) lamps. MASTER – LED HID SON-T solutions bring the energy efficiency and long lifetime benefits of LED to HID replacement, providing instant savings for a low initial investment. With the right lamp size and light distribution, you can easily retrofit MASTER – LED HID SON-T lamps into existing SON and SON-T systems, enhancing the lighting quality with LED without changing the luminaire's ballast (for IF replacements) or reflector.

#### Warnings and Safety

· Please refer to the installation guide or consult a Philips Lighting representative for the wiring diagram and instructions.

#### **Product data**

| General Information                |                    |  |
|------------------------------------|--------------------|--|
| Cap-Base                           | E27                |  |
| Nominal lifetime                   | 70,000 hour(s)     |  |
| Switching Cycle                    | 50,000             |  |
| Lighting Technology                | LED                |  |
| Flux measurement reference         | Sphere             |  |
|                                    |                    |  |
| Light Technical                    |                    |  |
| Color Code                         | 740 [CCT of 4000K] |  |
| Luminous Flux                      | 4,000 lm           |  |
| Luminous Efficacy (rated) (Nom)    | 173 lm/W           |  |
| Color Designation                  | Cool White (CW)    |  |
| Correlated Color Temperature (Nom) | 4000 K             |  |
| Color Consistency                  | <6                 |  |

| Color rendering index (CRI)                  | 70      |
|--|---------|
| LLMF At End Of Nominal Lifetime (Nom)        | 70 %    |
| Photobiological safety according to EN 62471 | RG1     |
|  |         |
| Operating and Electrical                     |         |
| Line Frequency                               | 50 Hz   |
| Input Frequency                              | 50 Hz   |
| Power Consumption                            | 23 W    |
| Lamp Current (Nom)                           | 775 mA  |
| Starting Time (Nom)                          | 0.5 s   |
| Warm-up time to 60% light                    | 0.5 s   |
| Power Factor (Fraction)                      | -       |
| Voltage (Nom)                                | 48-58 V |
| Inrush current at mains                      | -       |


Datasheet, 2024, July 15 data subject to change

# **MASTER - LED HID SON-T**

| Max. lamp no. on MCB B type 10A - Mains       | -             |
|---|---------------|
| Max. lamp no. on MCB B type 10A – EM ballast  | 9             |
| without Compensation Capacitor.               |               |
| Max. lamp no. on MCB B type 10A – EM ballast  | 14            |
| with Compensation Capacitor.                  |               |
| Max. lamp no. on MCB B type 16A - Mains       | -             |
| Max. lamp no. on MCB B type 16A – EM ballast  | 14            |
| without Compensation Capacitor.               |               |
| Max. lamp no. on MCB B type 16A – EM ballast  | 22            |
| with Compensation Capacitor.                  |               |
| Ballast Compatibility                         | EM            |
|   |               |
| Temperature                                   |               |
| Ambient temperature range                     | -30 to +45 °C |
| T-Case Maximum (Nom)                          | 46 °C         |
|   |               |
|   |               |
| Controls and Dimming                          |               |
| Controls and Dimming Dimmable                 | No            |
|   | No            |
|   | No            |
| Dimmable                                      | No Clear      |
| Dimmable  Mechanical and Housing              |               |
| Dimmable  Mechanical and Housing  Bulb Finish | Clear         |

| Approval and Application        |                               |
|---------------------------------|-------------------------------|
| Energy Efficiency Class         | С                             |
| Energy Consumption kWh/1000 h   | 23 kWh                        |
| EPREL Registration Number       | 1077792                       |
| EU RoHS compliant               | Yes                           |
|                                 |                               |
| Product Data                    |                               |
| Order product name              | MAS LED SON-T IF 4Klm 23W 740 |
|                                 | E27                           |
| Full product name               | MAS LED SON-T IF 4Klm 23W 740 |
|                                 | E27                           |
| Full product code               | 871951444889600               |
| Order code                      | 929003467112                  |
| Material Nr. (12NC)             | 929003467112                  |
| Numerator - Quantity Per Pack   | 1                             |
| Net Weight (Piece)              | 0.250 kg                      |
| EAN/UPC - Product/Case          | 8719514448896                 |
| Numerator - Packs per outer box | 6                             |
| EAN/UPC - Case                  | 8719514448902                 |
|                                 |                               |


# Dimensional drawing



| Product                           | D     | С      |
|-----------------------------------|-------|--------|
| MAS LED SON-T IF 4Klm 23W 740 E27 | 61 mm | 200 mm |


# **MASTER - LED HID SON-T**

#### Photometric data




Calculat Phesonetric 4.5 Philips Lighting B.V. Physi-

General uniform lighting - MAS LED SON-T IF 4Klm 23W 740 E27




100

Spectral Power Distribution Colour - MAS LED SON-T IF 4Klm 23W 740 E27




Light Distribution Diagram - MAS LED SON-T IF 4Klm 23W 740 E27

#### Lifetime



3



Lumen Maintenance Diagram - MAS LED SON-T IF 4Klm 23W 740 E27

Life Expectancy Diagram

# **MASTER - LED HID SON-T**



© 2024 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.