


REV.	DATE	DESCRIPTION
A	01/13/99	ADD CRIMP NOTES / CHANGE FERRULE DIMS.



NOTE:  
 USE .151 HEX CRIMP DIE TO  
 FORMATE FERRULE TO CABLE.  
 -- CONNEX TOOL 47-10160  
 -- IDEAL TOOL N6-469

DESCRIPTION	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN ( ) ARE IN INCHES FOR CUSTOMER REFERENCE ONLY	APPROVALS	DATE
1 HOUSING	BRASS	NICKEL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS AND TOLERANCES FOR MILLIMETERS ARE: 0.5-6 = ± 0.2 6-30 = ± 0.4 30-120 = ± 0.6 120-1000 = ± 1 1000-2000 = ± 1.6 2000-5000 = ± 2.4 DO NOT SCALE DRAWING	DRAWN	01/13/99
2 BODY	BER. COPPER	NICKEL		CHECKED	
3 INSULATOR-1	TEFLON	NATURAL		DESIGNED	
4 CONTACT PIN	BRASS	GOLD			
5 INSULATOR-2	DELIN	NATURAL			
6 COVER	BRASS	NICKEL			
7 FERRULE	COPPER	NICKEL			
8					



TITLE	MCX R/A CRIMP PLUG
SIZE	RG 174/u, 316/u DOUBLE BRAIDED CABLE
REV.	A
FSCM NO.	99001
DWG. NO.	252118.DWG
SCALE	NA
PART NO.	252118
SHEET	1 OF 1