



Sample photo

**Order symbol:** P 081606  
**Product nbr:** 7094170  
**Description:** Enclosure  
**Remarks:** Polyester

**EAN:** 6418074004352  
**EI. number:**  
 Finland: 3423657  
 Electric No. Denmark: 8212005620  
 Electric No. Italy: 7331020  
 Electric No. Sweden: 2536209

Including: Base, cover with EPDM gasket and stainless steel cover screws.

Dimensions:	Length	Width	Height	Rating:
mm:	160	75	55	Ingress Protection (EN 60529): IP66
inch:	6.3	3.0	2.2	Impact Resistance (EN 62262): IK08
<b>Materials:</b>				Electrical insulation: Totally insulated
<b>Material:</b>	Polyester			Halogen free (DIN/VDE 0472, Part 815): 1
<b>Base colour:</b>	RAL 7001			UV resistance: UL 508
<b>Cover screws material:</b>	Stainless steel			Flammability Rating: UL 746C 5V
<b>Cover colour:</b>	RAL 7001			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Gasket material:</b>	EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
<b>Temperatures:</b>				
<b>Temperature °C (short term):</b>	-50 ... 120 °C			
<b>Temperature °C (continuous):</b>	-40 ... 80 °C			
<b>Temperature °F (short term):</b>	-60 ... 250 °F			
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			

EURONORD P 160x75x55

