


Crimp Fittings

Press-armaturen

Embouts sertis

Raccordi a graffare

Racores para presión



KSB

Komatsu Split Flange, 90° Elbow

Komatsu Flansch, 90° Krümmer

Bride Komatsu, coudé 90°

Flangia Komatsu a 90°

Brida Komatsu acodado a 90°

Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
	1S10KSB10	1A10KSB10					-10	69,7	40,3	51,4	11,7			34,2
	1S12KSB12						-12	87,0	56,8	52,4	15,5			38,1
	1S16KSB16	1A16KSB16					-16	109,5	75,1	70,5	20,7			44,5
	1S20KSB20						-20	130,7	86,7	80,4	26,6			50,8
	1S24KSB24	1A24KSB24					-24	151,0	104,7	108,5	32,0			60,3
	1S32KSB32						-32	200,5	148,3	140,0	44,4			71,4