



Datasheet for part number CA06COMPG18-10PB

Our Catalog Part Number: CA06COM-PG18-10P-B
Our Global Manufacturing Part Number: 121576-0143
Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA COM-B

Product Datasheet	
Bayonet	Connector with Bayonet Coupling
Shell Style	Plug, straight
Endbell Style	Endbell for PG cable gland termination
Gender	Pin
Shell Size	18
Contact Arrangement	18-10
Number of contacts	4 contacts size 12
Contact Type	Solder Cup
Contact Plating	Hard silver
Contacts installed	yes
Contact Rating at +20 °C (68 °F) (Size 25/12)	41 A
Contact Resistance (Size 25/12)	3 mΩ
Operating Voltage	In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.
Insulator Resistance	≥1000 MΩ
Test Voltage	1600 Vrms
Air and Creepage Paths (Min)	1,1 mm
Ambient Temperature	Standard insulator material -55°/+125°C (-67/257°F)
Safety Provisions	IP67 (only applies if a grommet is used)
Mating Cycles	500 min
Sep. Force per Contact (Size 25/12)	1,5 N
Gage	For infos on Gage please see catalog VG95234, part 1
Coupling Torque	Closing: 4 Nm max / Opening: 0,58 Nm min
Contact Retention (Size 25/12)	55 N
Shell Material	Aluminium alloy
Shell Plating	Nickel plated
Insulator and Gromet Material	CR-Elastomere
Contact Material	Copper alloy
Harnessing Info: Contact Cross-Section	See assembly instruction
Harnessing Info: Insulator Diameter	See assembly instruction
Wire Stripping (Size 25/12)	6,2 mm
General Info	<i>All tests in accordance with VG95319 and/or if applicable with VG95210 except salt spray resistance and heat and humidity endurance test</i>