

RATING CHARTS

ENCLOSED L SERIES

INPUT		OUTPUT				TYPE	APPROXIMATE WEIGHT (POUNDS)		
VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD		NET	SHIPPING	
			MAX. AMP.	MAX. KVA.	MAX. AMP.				MAX. KVA.
120	60	0-132	1.75	.23	---	---	L10C	5 lb.,	6 lb.,
120	50/60	0-140	4.5	.63	---	---	L21C	10 lb.,	11 lb.,
120	50/60	0-140	10	1.4	---	---	L116C	14 lb.,	15 lb.,

LINE CORRECTOR SERIES**

INPUT		OUTPUT		MANUALLY OPERATED				MOTOR DRIVEN			
VOLTS	HERTZ	VOLTS	MAX. AMP.	MAX. KVA.	TYPE	APPROXIMATE WEIGHT (POUNDS)		TYPE	AVAILABLE SPEEDS (SECONDS) AT 60 HZ □ □ □	APPROXIMATE WEIGHT (POUNDS)	
						NET	SHIPPING			NET	SHIPPING
95-135	50/60	115	57	6.6	LC2106D	66	81	MDLC2106D	5, 15, 30, 60	79	99
95-135	50/60	115	144	16.6	LC2115E	117	202	MBLC2115E	5, 15, 30, 60	197	227
195-255	50/60	230	36	8.3	LC2207D	68	83	MDLC2207D	5, 15, 30, 60	81	101
205-250	50/60	230	130	29.9	LC2228E	183	208	MBLC2228E	5, 15, 30, 60	213	243
400-520	50/60	460	45	20.7	LC2418E	177	202	MBLC2418E	5, 15, 30, 60	197	227
195-255	50/60	230	63	25.1	LC3220YD	204	229	MDLC3220YD	5, 15, 30, 60	222	252
195-255	50/60	230	145	57.8	LC3245YE	551	631	MBLC3245YE	5, 15, 30, 60	565	650
195-255	50/60	230	188	74.9	LC3270DE	560	670	MBLC3270DE	15, 30, 60	580	695
400-520	50/60	460	35	27.9	LC3425YD	210	235	MDLC3425YD	5, 15, 30, 60	228	258
400-520	50/60	460	100	79.7	LC3475YE	536	616	MBLC3475YE	5, 15, 30, 60	550	635
420-500	50/60	460	148	118	LC34100YE	536	616	MBLC34100YE	5, 15, 30, 60	550	635

single phase

three phase

Line correctors may also be used as limited range transformers. Input voltage is the output voltage shown in the chart and output voltage is the input voltage shown in the chart. Maximum voltage limited by saturation characteristics of transformer core. 60 hertz only. Speeds are 20 percent slower at 50 hertz.

AUXILIARY EQUIPMENT

TYPE	DESCRIPTION	TYPE	DESCRIPTION	TYPE	DESCRIPTION
096-000	Raise-Lower Switch	26602-008	Control Potentiometer For FR501B	T5579B	3-Gang Paralleling Choke for 136B, 236B, 246 Series
120B	Position Detector	T6026	Transformer for Full Range Regulator Controllers	T5587	Paralleling Choke supplied with all 1156D-1256D Series
302-008	Position Control Potentiometer	T6340	Transformer for Full Range Regulator Controllers	T6053	2-Gang Paralleling Choke for 146 Series
068	Transformer for Positioner Detector	B211060-1	Potentiometer Adapter Kit for 10C Series	T6065	3-Gang Paralleling Choke for 146 Series
501B*	Full Range Regulator Controller For A-C Voltage Control	30111-000	Potentiometer Adapter Kit for 12 Series		
501BMP*	Full Range Regulator Controller with Meter and Control	T5000B	2-Gang Paralleling Choke 136B, 236B, 246 Series		
501BDC*	Full Range Regulator Controller For D-C Voltage Control				

*Add suffix X when ordering for use with X-suffixed motor-driven POWERSTAT Variable Transformers.

REPLACEMENT BRUSHES

UNIT TYPE‡	BRUSH TYPE	UNIT TYPE‡	BRUSH TYPE	UNIT TYPE‡	BRUSH TYPE	UNIT TYPE‡	BRUSH TYPE	UNIT TYPE‡	BRUSH TYPE	UNIT TYPE‡	BRUSH TYPE
		116C	RB116B	226	RB226	146	RB146	Q116U	RBQ116	Q217U	RBQ217
						246	RB246			LW136B	RBLW136
10C	RB10B	117C	RB117B	136B, LC2106D LC3220YD	RB136	1156D, LC2115E LC2418E, LC3245YE	RB1156B	Q117U	RBQ117	10C-40	RB10B-40
12	RB12	216C	RB216B			1256D, LC2228E LC3270DE, LC3475YE, LC34100YE	RB1256B	Q216U	RBQ216	21-40	RB21-40
21	RB21	217C	RB217B	236B, LC2207D LC3425YD	RB236					116CU-40	RB116B-40
22	RB22	126	RB126								

‡ Includes also ganged units and variations such as Enclosed, Oil-Cooled and Explosion-proof types.