

SAI-M23-BE-L-6**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Type	SAI-M23-BE-L-6
Order No.	1170370000
Version	Sensor/Actuator plug-in connector, Insert
GTIN (EAN)	4032248962266
Qty.	1 pc(s).

SAI-M23-BE-L-6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 8.5 g

Temperatures

Operating temperature, max. 125 °C Operating temperature, min. -40 °C

Standards

Certificate No. (UR) E344862

General data

Coding	none	Conductor O.D.	-
Contact number / diameter	6 x 2 mm	Contact surface	Gold-plated
Design	Female	Fire behaviour	V-0
Housing main material	Thermoplastic polyamide PA 6, PBT	Insulation resistance	> 10 ¹³ Ω
No. of poles	6	Plugging cycles	> 1000
Type of connection	Crimp connection	connection thread	M23

Classifications

ETIM 5.0	EC002635	ETIM 6.0	EC000438
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.0	27-06-91-90
eClass 9.1	27-44-02-05		

Product information

Product information Enclosures, inserts and crimp contacts need to be ordered separately.

Approvals

Approvals



ROHS Conform

Downloads


Brochure/Catalogue [CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)

SAI-M23-BE-L-6

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Drawings

Dimensioned drawing



Technical data

No. of poles	5 + PE	4/4	
Number of contacts	6	4	4
Contact-ø	mm 2	1	2

6 times female, 2 mm