

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510471000](#)
Status: **Active**
Overview: [PicoBlade Connector System](#)
Description: 1.25mm Pitch PicoBlade Wire-to-Wire Plug Housing, 10 Circuits, Natural

Documents:

[3D Model](#) [Product Specification PS-51021-009-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [51047](#)
 Application Signal, Wire-to-Wire
 Current Derating Order No 987651-3691
 Overview [PicoBlade Connector System](#)
 Product Name PicoBlade
 UPC 800753756946


Physical

Circuits (maximum) 10
 Color - Resin Natural
 Gender Plug
 Glow-Wire Capable No
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 171.100/mg
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 1.25mm
 Stackable No
 Temperature Range - Operating -40° to +85°C

Material Info

Reference - Drawing Numbers

Product Specification PS-51021-009-001
 Sales Drawing SD-51047-**00



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51047 Series](#)

Mates With

[51021 Housing](#)

Use With

[50125 Crimp Terminal](#), [50133 Crimp Terminal](#)