

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2153131022](#)
Status: **Active**
Overview: Mizu-P25 Miniature Waterproof Connectors
Description: Mizu-P25 Male-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 2.50mm Pitch, Waterproof, Single Row, 300.00mm Length, Tin (Sn) Plating, 2 Circuits, Black

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	215313
Application	Signal, Wire-to-Wire
Assembly Configuration	Single Ended Connector
Connector to Connector	Mizu-P25-to-Pigtail
Overview	Mizu-P25 Miniature Waterproof Connectors
Product Name	Mizu-P25 Waterproof
Type	Discrete Wire Assembly, Sealed Assembly
UPC	193264682676

Physical

Cable Length	300.00mm
Circuits (Loaded)	2
Color - Resin	Black
Gender	Male-Pigtail
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Resin	Polyester
Net Weight	5.170/g
Number of Rows	1
Pitch - Mating Interface	2.50mm
Single Ended	Yes
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.90mm
Wire Size AWG	20, 22
Wire/Cable Type	PVC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Sales Drawing	2153131021-000
---------------	----------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2020)4578-DC (25
June 2020)
pentacosafuorotridecanoic
acid
1,2-
Benzenedicarboxylic
acid, dihexyl ester,
bra
Terphenyl,
hydrogenated
2-(2H-benzotriazol-2-
yl)-4-(tert-butyl)-6-
(sec-b
2-(2H-benzotriazol-2-
yl)-4,6-
ditertpentylphenol
2-ethylhexyl 10-
ethyl-4,4-dioctyl-7-
oxo-8-oxa-3,
sodium
peroxometaborate
ammoniumpentadecafluorooctanoate
disodium 4-
amino-3-[[4'-[(2,4-
diaminophenyl)azo]
1,3-propanesultone
1-vinylimidazole
1,2-diethoxyethane
disodium 3,3'-[[1,1'-
biphenyl]-4,4'-
diylbis(azo)
dodecamethylcyclohexasiloxane
perfluorooctanoic acid
di-n-pentyl phthalate
(DPP)
furan
4-o-tolylazo-o-
toluidine

China RoHS

ethylene thiourea
4-methyl-m-phenylenediamine
o-toluidine
butyl 4-hydroxybenzoate
phenanthrene
dicyclohexyl phthalate
p-(1,1-dimethylpropyl)phenol
N-methylacetamide
1,2-benzenedicarboxylic acid, dipentylester, bra
Perfluorohexane-1-sulphonic acid and its salts
5-sec-butyl-2-(2,4-dimethylcyclohex-3-en-1-yl)-5
1,2-benzenedicarboxylic acid, di-C6-10-alkyl est
reaction mass of 2-ethylhexyl 10-ethyl-4,4-dioct Cadmium sulphate
Bisphenol-A
Methylhexahydrophthalic anhydride
Perfluorononan-1-oic acid
(2,2,3,3,4,4,5,5,6,6,7 Reaction products of 1,3,4-thiadiazolidine-2,5-d
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Pyrene
Perfluorobutane sulfonic acid (PFBS) and its sal
Tris(4-nonylphenyl, branched and linear) phosphi
Nonadecafluorodecanoic acid (PFDA) and its sodiu
4-Nonylphenol, branched and linear, ethoxylated
Trixylyl phosphate
4-Nonylphenol, branched and linear
[substances w
Zirconia
Aluminosilicate
Refractory Ceramic Fibr
Aluminosilicate
Refractory Ceramic Fibres
4,4'-Oxydianiline and its salts

Boric acid
Disodium tetraborate
n-pentyl-
isopentylphthalate
3-ethyl-2-methyl-2-
(3-methylbutyl)-1,3-
oxazolidi
2-benzyl-2-
dimethylamino-4-
morpholinobutyropheno
2-methyl-1-(4-
methylthiophenyl)-2-
morpholinoprop
pentazinc chromate
octahydroxide
trilead diarsenate
arsenic acid
potassium
hydroxyoctaoxodizincatedichromate(1-)
1,2-
benzenedicarboxylic
acid; di-C6-8-
branched a
1,2,3-trichloropropane
N-methyl-2-
pyrrolidone
1,2-
benzenedicarboxylic
acid; di-C7-11-
branched
2-ethoxyethyl acetate
cobalt sulphate
cobalt dinitrate
cobalt carbonate
2-ethoxyethanol
trichloroethylene
tetraboron disodium
heptaoxide, hydrate
potassium dichromate
potassium chromate
Pitch, coal tar, high-
temp.; Pitch
Lead chromate
molybdate sulfate red
lead chromate
Anthracene oil,
anthracene-low;
Anthracene Oil F
lead hydrogen
arsenate
bis(2-ethylhexyl)
phthalate (DEHP)
diarsenic trioxide
dibutyl phthalate
(DBP)
4,4'-
diaminodiphenylmethane
bis(2-methoxyethyl)
phthalate
dimethyl sulphate
benzo[a]pyrene
Fatty acids, C16-18,
lead salts
[phthalato(2-)]dioxotrilead

Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Sulfurous acid, lead
salt, dibasic
lead
bis(tetrafluoroborate)
dioxobis(stearato)trilead
tetralead trioxide
sulphate
lead titanium trioxide
lead oxide sulfate
Silicic acid, lead salt
lead dinitrate
cadmium
lead
[4-[[4-anilino-1-
naphthyl]]4-
(dimethylamino)phen
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
Lead oxide
trilead bis(carbonate)
dihydroxide
orange lead
cadmium oxide (non-
pyrophoric)
diboron trioxide
cadmium carbonate
N,N,N',N'-
tetramethyl-4,4'-
methylenedianiline
2,2'-dichloro-4,4'-
methylenedianiline
dichromium
tris(chromate)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[215313](#) Series

Mates With

[52213](#) Mizu-P25 2.50mm Pitch Waterproof
Wire-to-Wire Receptacle Housing

This document was generated on 10/15/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION