

Spacer sleeve for MK with clamping thread (DIN 6364)

in accordance with ISO 7388-1

ATORN[®]

Application

For holding tools with Morse taper shank in accordance with DIN 228 A with clamping thread.

Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm²
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm, bronzed
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- max. concentricity < 0.005 mm



Art. no.	23163 040
Mount, on tool side	MK 3
Projecting length	65 mm
Outer diameter	40 mm
Tool holding device	SK 50

EAN-Code

4050293713107