




1 2 3 4 5 6 7 8

A



B



**MATERIALS**

- 1. HOUSING : P.B.T. (UL 94V-0), BLACK.
- 2. TERMINAL : S.Q. 0.64mm GOLD PLATING.


**SPECIFICATION**

- 1. CURRENT RATING : 3 AMP. MAX.
- 2. DIELECTRIC WITHSTANDING VOLTAGE : 1000V AC R.M.S. FOR ONE MINUTE.
- 3. INSULATION RESISTANCE : 5000M OHMS MIN. AT 1000V DC.
- 4. OPERATING TEMPERATURE : -55°C TO +105°C.

D

Dimensions			
Pos.	A	B	C
10	32.00	27.94	10.16
14	37.08	33.02	15.24
16	39.62	35.56	17.78
20	44.70	40.64	22.86
24	49.78	45.72	27.94
26	52.32	48.26	30.48
30	57.40	53.34	35.56
34	62.48	58.42	40.64
40	70.10	66.04	48.26
50	82.80	78.74	60.96

E



F

玄茂科技股份有限公司  
HSUAN MAO TECHNOLOGY CO., LTD.

UNIT		SCALE	PART NAME	
MM			2.54x2.54mm FULLY SHROUDED HEADER 180° LONG LATCH	
APPD.	CKD.	TOLERANCE	PART NO.	REV.
			C3000-XXSLXB00R	A

H

制表日: 2006/01/10

DRAWING. APPROVED  
*Jolin*

1 2 3 4 5 6 7 8