

Between Series Adaptor 33_BNC-QLA-01-1/1--_N

Description

Adaptor plug/jack
BNC plug (male) / QLA-01 jack (female)

Interface standards
Series BNC - IEC 61169-8_MIL-STD-348A/301_CECC 22120
Series QLA-01 - NIM-CAMAC-Standard CD/N549



Technical Data

Electrical Data

Impedance other Ω
Interface frequency max. 1.4 GHz

Mechanical Data

Number of matings 500
Weight 0.0125 kg

Environmental Data

Operating temperature -55 °C to 155 °C
2011/65/EU (RoHS - including
2015/863 and 2017/2102) compliant

Material Data

Interface - BNC plug (male)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Interface - QLA-01 jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (without Nickel underplating)
Outer contact	Bronze	Gold Plating (Nickel underplated)
Body	Brass	Nickel Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing DCA-00014383

Ordering Information

Single package 33_BNC-QLA-01-1/1--_NE