


E73009



Wall passage

Wall passage stainless steel



Electrical data

Operating voltage [V]	< 60 AC/DC
Max. current load total [A]	8; (Pin 1+3: 4 A; Pin 2+4: 4 A)

Operating conditions

Ambient temperature [°C]	-40...85
Protection	IP 65; IP 67; IP 69K

Mechanical data


Weight [g]	29.5
Materials	stainless steel (1.4305 / 303); Sealing: EPDM
Tightening torque [Nm]	1

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12, straight; Moulded body: stainless steel (1.4305 / 303)




E73009



Wall passage

Wall passage stainless steel

Connection



Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: stainless steel (1.4305 / 303)

