










Model Number

NBB5-18GM60-WS

Features

- **Basic series**
- 5 mm embeddable
- 2-wire AC

Connection



Accessories


EXG-18

Quick mounting bracket with dead stop

BF 18

Mounting flange, 18 mm

Dimensions



Technical Data

| General specifications | | | | | | | |
|--|----------------|----------|-----|--|--|--|--|
| Switching element function | | AC | NO | | | | |
| Rated operating distance | s _n | 5 mm | | | | | |
| Installation | | embeddab | ole | | | | |
| Output polarity | | AC | | | | | |
| Assured operating distance | sa | 0 4.05 r | mm | | | | |
| Reduction factor r _{Al} | | 0.2 | | | | | |
| Reduction factor r _{Cu} | | 0.2 | | | | | |
| Reduction factor r ₃₀₃ | | 0.6 | | | | | |
| Nominal ratings | | | | | | | |
| Operating voltage | U_B | 20 253 | V | | | | |
| Consideration on fundamental and an account of the contract of | | 0 00 11- | | | | | |

Switching frequency 0 ... 20 Hz Н Hysteresis typ. 6 % Reverse polarity protected tolerant < 5 V (I_L > 50 mA); < 8 V (I_L < 50 mA) Voltage drop U_{d} Momentary current (20 ms, 0.1 Hz) 0 ... 1600 mA Operating current
Off-state current 5 ... 200 mA 0 ... 1.7 mA typ. Operating voltage display LED, green Indication of the switching state LED, yellow

Ambient conditions

Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

Mechanical specifications

cable PVC , 2 m $0.34~\text{mm}^2$ Connection type Core cross-section Housing material brass, nickel-plated Sensing face 1) In the temperature range below 0 °C, permissible operating voltage U_b 80...253 V Safety fuse \leq 0.8 A (quick-blow) according to IEC 60127-2 Sheet 1 Protection degree Note

Recommendation: after a short circuit, check that the device is

functioning correctly.

Compliance with standards and directives

| Standard conformity | |
|---------------------|--------------------|
| Standards | EN 60947-5-2:2007 |
| | IEC 60947-5-2:2007 |

Approvals and certificates

| • • | |
|--------------|---|
| UL approval | cULus Listed, General Purpose |
| CSA approval | cCSAus Listed, General Purpose |
| CCC approval | Certified by China Compulsory Certification (CCC) |

Pepperl+Fuchs Group www.pepperl-fuchs.com