



MEHRBEREICHSBLINDNIETE FLACHRUNDKOPF

MULTIGRIP BLIND RIVETS DOMED HEAD


RIVETS MULTI SERRAGE TÊTE PLATE









Aluminium AIMG 2,5 **RAL 9005 schwarz**
Aluminium AIMG 2,5 **RAL 9005 black**
Aluminium AIMG 2,5 **RAL 9005 noir**


Stahl verzinkt
Steel zinc plated
Acier zingué







Ø 3,0 mm

D1 = 3,0 + 0,05 / - 0,13 mm
D2 = 6,0 + 0 / - 0,24 mm
k = ≤ 1,4 mm
d = 1,7 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,1 mm


	F-Max		CODE				
3,0 x 8,0 mm	11,5 mm	1,0 - 5,5 mm	79005 30803	520 N	650 N	1000	10000
3,0 x 10,0 mm	13,5 mm	2,5 - 7,0 mm	79005 30103			1000	10000
3,0 x 12,0 mm	15,5 mm	4,5 - 9,0 mm	79005 30123			1000	10000







Ø 3,2 mm

D1 = 3,2 + 0,05 / - 0,13 mm
D2 = 6,0 + 0 / - 0,24 mm
k = ≤ 1,4 mm
d = 1,78 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 3,3 mm

	F-Max		CODE				
3,2 x 8,0 mm	12,0 mm	1,0 - 5,0 mm	79005 32803	630 N	930 N	1000	10000
3,2 x 9,5 mm	13,5 mm	1,3 - 6,4 mm	79005 32953			1000	10000
3,2 x 10,0 mm	14,0 mm	2,5 - 7,0 mm	79005 32103			1000	10000
3,2 x 11,1 mm	15,1 mm	4,0 - 7,9 mm	79005 32113			1000	10000
3,2 x 12,0 mm	16,0 mm	4,5 - 9,0 mm	79005 32123			1000	10000
3,2 x 14,0 mm	18,0 mm	6,5 - 11,0 mm	79005 32143			1000	10000
3,2 x 16,0 mm	20,0 mm	8,5 - 13,0 mm	79005 32163			1000	10000

Ø 4,0 mm

D1 = 4,0 + 0,05 / - 0,13 mm
D2 = 8,0 + 0 / - 0,29 mm
k = ≤ 1,7 mm
d = 2,18 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm
 4,1 mm

	F-Max		CODE				
4,0 x 8,0 mm	12,0 mm	1,0 - 5,0 mm	79005 40803	1050 N	1300 N	1000	10000
4,0 x 9,5 mm	13,5 mm	1,2 - 6,4 mm	79005 40953			1000	10000
4,0 x 10,0 mm	14,0 mm	1,5 - 6,5 mm	79005 40103			1000	10000
4,0 x 12,0 mm	16,0 mm	3,5 - 8,5 mm	79005 40123			1000	10000
4,0 x 12,7 mm	16,7 mm	4,0 - 9,5 mm	79005 40127			1000	10000
4,0 x 16,0 mm	20,0 mm	6,0 - 12,5 mm	79005 40163			500	5000
4,0 x 17,0 mm	21,0 mm	6,4 - 13,5 mm	79005 40173			500	5000
4,0 x 20,0 mm	24,0 mm	11,5 - 16,5 mm	79005 40203			500	5000