

THH.631.B5A

TeeBox Power distribution Connector 7mm to 14mm cable max IP65 rated Screw fixing 3 cable entries, 5 poles contact screw terminals 17.5A 400V



Temperature "T" rating	T85
Minimum cable diameter (mm)	7
Maximum cable diameter (mm)	14
Fixing system	Screw
Cable entries	3
Number of poles	5
Terminal type	Screw
Body material	PA66/TPE/SEBS
Max current (A)	17.5
Max voltage (V)	400
Minimum temp rating °C	-40
Max temp rating °C	125
IP rating	65