

## MB4A10C2

Article Number: 151-28421

Adhesive Bases, .18" Max tie width, 1.12" Length/Width, .18" Hole Dia., PA66, White, 100/pkg



Download spec sheet

### Base Data

Local Order Number MB4A10C2

Type MB4A

Color White (WH)

- Features and Benefits**
- For use with 18 and 30 pound cable ties to provide stability when securing bundles.
  - Secures with rubber based adhesive backing and/or two or four screws.
  - 4 way opening allows cable ties to be installed parallel or perpendicular to wire bundles.

**Product Description** HellermannTyton adhesive fastened mounting bases are used with 18 through 150 pound cable ties to provide stability when securing bundles. The mounts are installed using the adhesive backing and/or by securing two or four screws. The 4 way opening allows the cable ties to be inserted parallel or perpendicular to the wire bundles.

**Short Description** Adhesive Bases, .18" Max tie width, 1.12" Length/Width, .18" Hole Dia., PA66, White, 100/pkg

### Product Dimensions

Length L (Imperial) 1.12 "

Length L (Metric) 28.5 mm

Fixation Method Screw Mounting and Adhesive

Width W (Imperial) 1.12 "

Width W (Metric) 28.5 mm

Cable Tie Width Max. (Imperial) 0.18 "

Cable Tie Width Max. (Metric) 4.6 mm

Height H (Imperial) 0.22 "

Height H (Metric) 5.6 mm

Mounting Hole Diameter D (Imperial) 0.18 "

Mounting Hole Diameter D (Metric) 4.6 mm

Mounting Hole Centers (Imperial) 0.8 "

Mounting Hole Diameter D Max. (Metric) 4.6 mm

Mounting Hole Diameter D Min. (Metric) 4.6 mm

### Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 4000

### Material and Specifications

Material Polyamide 6.6 (PA66)

**Material Shortcut** PA66

**Adhesive** Synthetic rubber with base of polyethylene foam

**Flammability** UL94 V2 (excluding adhesive)

**Operating Temperature** -40°F to +185°F (-40°C to +85°C)

**ROHS Compliant** Yes

**UL Listed (US and Canada)** No

**UL Recognized (US and Canada)** Yes