

Twist drill type N with soldered cemented carbide insert 4xD

For universal use up to 1500 N/mm²

ORION[®]

Application:

Universal use in all material groups up to a strength of 1500 N/mm².

Execution:

- Twist drill with universal standard geometry, soldered cemented carbide insert (K20) and driving lug on the clamp shank

Advantage:

- Cemented carbide insert, K20, for a long service life
- polished chipping spaces ensure good chip removal
- cost-effective tool for broad range of applications



Art. no.	11160 150
Brand	ORION
Manufacturer Part Number	11160150
Cutting edge diameter	15 mm
Chip flute length	71 mm
Length	125 mm
f steel 1300	0.17 mm/r
DIN	8037
Gross Weight	0.130 kg
Product Group	140

EAN

4039247030071